

Crimp splice protection - FOC-CRIMPSPLICE-PROTECT - 1019678

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp splice protection, type: Straight, degree of protection: IP20, connection method: Crimp, cable outlet: above and below, color: Bare metallic

Product Description

Crimp splice protection in blister packaging

Your advantages

- ✓ No attenuating effects on the fusion splice
- ✓ Mechanical protection for fusion splices
- ✓ Telekom TS 0338/96 approval

RoHS

Key Commercial Data

Packing unit	12 pc
Minimum order quantity	12 pc
GTIN	 4 055626 701189
GTIN	4055626701189

Technical data

Mechanical characteristics

Connection method	Crimp
External cable diameter	250 µm (Includes primary coating)
Cable outlet	above and below
Color	Bare metallic
Mounting type	Crimp splice protection
Degree of protection	IP20
Type	Straight
Type of note	Order information:
Note	Splice protection for FDX 20 splice boxes

Ambient conditions

Crimp splice protection - FOC-CRIMPSPLICE-PROTECT - 1019678

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (according to DIN EN 61300-2)
Degree of protection	IP20

Material data

Material	Metal
Depth	1.2 mm
Height	3 mm

Line characteristics

Cable type	Fiberglass
------------	------------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2019 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>