




REV. 0

DCO 141062


COIL: @ 25°C
 RESISTANCE 50 OHMS $\pm 10\%$
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 3.5 VDC
 MUST RELEASE 1.7 VDC MAX., 0.23 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX.
 RELEASE TIME 4.0 MS MAX.
 CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 5/13/99 CK *[Signature]* 5/13/99

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. QPL
 CUST. NO. M39016/24-019L

TYPE J1MADDRELAY

J1MAPDD-5XL