






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	㉑X3	产品尺寸变更，图面升级整理图面	2025.06.19	阿树



- SPECIFICATIONS
- Voltage rating: 250V AC/DC
 - Current rating: 7A AC/DC
 - Withstanding Voltage: 1500V AC/minute
 - Temperature range: -40°C~+125°C
 - Insulation resistance: ≥1000MΩ
 - Contact resistance: ≤20mΩ



PART NO.:
X5050 H M-XX-XX XX
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category: H-HSG
③Welding Board Angle:
M-Male housing
④Row No.Pin No: XX-02P
⑤Material: N0-PA66 UL94V-0
N2-PA66 UL94V-0
⑥Color: Blank-Natural Color

Poles	Dimensions(mm)		
	A	B	C
02	5.08	13.44	10.94
03	10.16	18.52	16.02
04	15.24	23.60	21.10

X5050HM-XX-N0	Nylon 66 UL 94V-0	X5050TF	X5050W X5050HF
X5050HM-XX-N2	Nylon 66 UL 94V-2		
PART NO	Material	Suitable XKB Terminal	Mates With XKB Wafer Or Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 5.08mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X5050HM-XX-N2
APPROVED		SIZE: A4	DWG NO.: