

4

3

2

1

NUMBER

C-172076

三角接 (3rd ANGLE PROJECTION)

9.0

"A"

"A"

27.8

7.2

8.3

△ ヒケ又は不貫通穴
SHRINK MARK AND/OR UNTHROUGH HOLE.

断面 "A" - "A"
(SECT "A" - "A")

10

-AMP

NOTES,

1. PRODUCT SPECIFICATION 108-5127

2. APPLICABLE CONTACT
P/N ; 170327,170328,170329

3. SEE CP78-26023. ABOUT APPLICABLE TAB.

△ MATERIAL ; 6/6 NYLON (94V-0)

△ THERE ARE A FEW CASES THAT SHRINK MARK AND/OR UNTHROUGH HOLE OCCURS IN THIS AREA, BUT NOT INFLUENCE TO CONN,FUNCTION.

△ COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT), (GWT, UL94V-0)

△ MATERIAL: PA66, UL94 V-0, GWIT 775°C

3-172076-1

NATURAL

△

OBSOLETE

7-172076-1

NATURAL

△

2-172076-7

(RED)

赤

△

2-172076-6

(BLUE)

青

△

OBSOLETE

2-172076-5

(GREEN)

緑

△

2-172076-4

(YELLOW)

黄

△

2-172076-2

(BLACK)

黒

△

2-172076-1

(NATURAL)

自然色

△

172076-7

(RED)

赤

172076-6

(BLUE)

青

172076-5

(GREEN)

緑

172076-4

(YELLOW)

黄

172076-2

(BLACK)

黒

172076-1

(NATURAL)

自然色

型番
(P/N)

色
(COLOR)

注
(NOTE)

PRINT DIST

単位: mm DIMENSIONS IN MM. DO NOT SCALE PRINT

DR.

17. JAN. '95

DE.

17. JAN. '95

CHK.

20. JAN. '95

APP.

20. JAN. '95

H. TAGUTCH

H. TAGUTCH

H7

REVISED PER ECR-19-018127

20JUL'20

AA

EW

H6

REVISED PER ECR-19-002938

25FEB'19

BH

E.W

REV

DESCRIPTION

DATE

DWN

APVD

TE Connectivity

250 シリーズ 1極 ポジティブロック (マークII)ハウジング
250 SERIES 1 Pos POSITIVE LOCK (MK-II) HOUSING

一般公差
(GENERAL TOLERANCE)
10以下: ±0.2
10を超え 30以下: ±0.25
30を超え 100以下: ±0.3
角 度: ±3°

LOC
B J

番号 (No.)
C-172076

尺度 (SCALE)
4-1

REV.
H7

SHEET
1 OF 1

(CUSTOMER DRAWING)

参 考 図 面