

## RAFIX 22 QR - Buzzer, round collar

1.30.249.002/0000



### General information

Form of lens	flat lens
Color of lens	opaque slate-grey
Sound	continuous beep

### Dimensions

Dimensions of collar	ø 29.8 mm
Overall height	9.8 mm
Mounting depth	56.4 mm
Mounting hole	ø 22.3 mm
Mounting grid	50 x 30 mm

### Mechanical design

Mounting	ring nut
----------	----------

### Electrical characteristics

Operating voltage DC	12 V
Input current	25 mA

### Acoustic characteristics

Sonic pressure, 1 m distance min.	70 dB
Sound frequency	2400 - 3100 Hz

### Other specifications

Degree of protection from front side	IP65 (DIN EN 60529)
Storage temperature min.	-40 °C
Storage temperature max.	+80 °C
Environmental resistance	acc. to IEC 60068-2-14, -30, -33 and -78
ROHS compliant	yes
REACH compliant	yes

Panel cut-out to IEC 60947-5-1



