






962-YYY-030R121
009 = 9 POSITION
025 = 25 POSITION

DIMENSIONS								
SIZE		A ^{±1.20} _{±0.047}	B ^{±1.20} _{±0.047}	C ^{±0.80} _{±0.031}	D ^{±0.80} _{±0.031}	E ^{±0.80} _{±0.031}	F ^{±0.80} _{±0.031}	G ^{±0.80} _{±0.031}
9	mm	15.00	30.80	15.00	24.40	50.80	18.00	26.20
	in.	0.59	1.21	0.59	0.96	2.00	0.71	1.03
25	mm	15.80	53.30	23.10	34.50	72.40	24.30	36.60
	in.	0.62	2.10	0.91	1.36	2.85	0.96	1.44

- BACKSHELL KIT INCLUDES:**
- (2) BACKSHELL HALVES
 - (3) HOUSING SCREWS (M2.6x0.45) (40 in-oz MAX.)
 - (1) 4-40 LONG FLAT HEAD SCREW (50 in-oz MAX.)
 - (1) 4-40 SHORT FLAT HEAD SCREW (50 in-oz MAX.)
 - (1) SET OF COMPRESSION INSERTS-VARIOUS SIZES (SEE DIAGRAM BELOW)

BACKSHELL MATERIAL: DIE CAST ZINC ALLOY, NICKEL PLATED
4-40 FLAT HEAD SCREWS: STEEL, ZINC PLATED
HOUSING SCREWS: STEEL, ZINC PLATED
COMPRESSION INSERT: ABS, UL RECOGNIZED
OPERATING TEMP: -40°C TO +120°C



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: B. BRIDGES
DATE: 02/14/2018

UNITS = "AS SPECIFIED" DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS
DWG NO.

SHEET 1 OF 1

REV 3

962-YYY-030R121