







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.06.13	阿树
/	N/A		/	/	/




2x06Pin




2x03Pin



2x02Pin



2x09Pin



2x04Pin

Specifications
Current rating: 3A AC,DC
Voltage rating: 250V AC,DC
Temperature range: -40*to+ 105*
Contact resistance: 10mΩ Max
Insulation resistance: 1000MΩ Min
Withstanding voltage: 800V AC/minute
Material: PA66 UL94V-0

PART NO.:

X2026 H-2xXX D B-N0 B
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category: H-HSG
③Row No.Pin No: 2xXX-2x02~2x22Pin
④Plug the Pin&special No:
DB-Without Lock in the middle
⑤Material: NO-PA66 94V-0
⑥Color: B-Black

X2026H-2xXXDB-N0B	PA66 UL 94V-0	X2026T-D-A
PART NO	Material	Suitable XKB Terminal

poles	Dimensions (mm)		poles	Dimensions (mm)	
	A	B		A	B
2x02	2.00	4.60	2x12	22.00	24.60
2x03	4.00	6.60	2x13	24.00	26.60
2x04	6.00	8.60	2x14	26.00	28.60
2x05	8.00	10.60	2x15	28.00	30.60
2x06	10.00	12.60	2x16	30.00	32.60
2x07	12.00	14.60	2x17	32.00	34.60
2x08	14.00	16.60	2x18	34.00	36.60
2x09	16.00	18.60	2x19	36.00	38.60
2x10	18.00	20.60	2x20	38.00	40.60
2x11	20.00	22.60			

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.00mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X2026H-2xXXDB-N0B
APPROVED		SIZE:	A4	DWG NO.:	