

NOTES :

△ MATERIALS AND FINISH:

- HOUSING: PA66

- CONTACTS: COPPER ALLOY, FINISH: TIN OVER NICKEL UNDERPLATE

- SPRING: STAINLESS STRIP STEEL

2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)

3. WIRE TYPES AND SIZES ACCEPTED

SOLID WIRE: 16AWG~20AWG.

STRIP LENGTH: 7.5mm~8.5mm



4. PACKAGED IN TRAY.

5. CURRENT RATING: 10Amp AC300V.

6. OPERATION TEMPERATURE: -40°C TO +105°C

REVISIONS

P	LTR	DESCRIPTION	DATE	BY	APP'D
A	1	FIRST VERSION	15JAN2015	GF	SM



DETAIL INNER


COLOR CODE: _____

SERIES CODE _____

PIN No: _____

1=GREEN	2=2 POSN
2=BLUE	3=3 POSN
3=BROWN	4=4 POSN
4=ORANGE	5=5 POSN
5=GREY	6=6 POSN
6=RED	7=7 POSN
7=YELLOW	8=8 POSN
8=PURPLE	
9=WHITE	
0=BLACK	

REMARK: THE DIFFERENT COLORS COULD BE COMBINED TO THE NEW CONNECTOR P/Ns FOR CUSTOMER REQUEST.



42.00	8 POSN
37.00	7 POSN
32.00	6 POSN
27.00	5 POSN
22.00	4 POSN
17.00	3 POSN
12.00	2 POSN
A	NO. OF POSITIONS

THIS DRAWING IS A CONTROLLED DOCUMENT

DATE: 15JAN2015

BY: GEORGE ELISABETH

CHK: SHI XIANG

REV: 15JAN2015

FILE: 108-137078

APP: 114-107078

VER: 1

CUSTOMER DRAWING

50mm Pitch Modular Screwless Conn.

TE Connectivity

SIZE: A2

CODE: 00779

SCALE: 1:1

SHEET: 1

REV: A