



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E		LC20-0097-18 / ECO-18-014539	08OCT2018	DM	BJ
F		LC20-0036-19 / ECO-19-005225	18APR2019	DM	BJ
G		LC20-0074-19 / ECO-19-010038	09AUG2019	DM	BJ
H		LC20-0091-20 / ECO-20-012656	08SEP2020	DM	BJ



(165 [6.5])	(64 [2.5])	ASBP-2-4/0-2.5	2182442-4
(330 [13])	(229 [9])	ASBP-2-4/0-9	2182442-3
(254 [10])	(152 [6])	ASBP-2-4/0-6	2182442-2
(406 [16])	(305 [12])	ASBP-2-4/0-12	2182442-1
DIM (Z)	DIM (Y)	CATALOG NO ²	PART NO

A/R	A/R	A/R	A/R	DESCRIPTION	ITEM NO
				METAL SEALANT	7
1	1	1	1	INSTALLATION INSTRUCTION SHEET, 408-32203	6
1	1	1	1	ABRASIVE TAPE	5
2	2	2	2	MULTI SHEAR HEAD BOLT, M14 SIZE, ALUMINUM ALLOY	4
A/R	A/R	A/R	A/R	INHIBITOR	3
1	-	-	-	EXPOSED LENGTH (64 [2.5])	2
-	1	-	-	EXPOSED LENGTH (229 [9])	
-	-	1	-	EXPOSED LENGTH (152 [6])	
-	-	-	1	EXPOSED LENGTH (305 [12])	
1	1	1	1	CONNECTOR SLEEVE BODY, ALUMINUM ALLOY, TIN PLATED	1
-4	-3	-2	-1		



- 1. ACCOMMODATES:
2 SOL - 4/0 STR.
- ² MARKING:
STE
[CATALOG NO]
2 SOL-4/0 STR
MADE IN [COUNTRY OF ORIGIN]
[DATE CODE]

(SEE TABLE FOR CATALOG NO MARKING)
- 3. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- 4. CONNECTOR CONTAINS FACTORY APPLIED ANTI-OXIDE INHIBITOR.
- 5. FINISH:
CU STUD AND AL CONNECTOR BODY ELECTRO-TIN PLATED.
- ⁶ INSTALL BOLTS WITH 13 mm [1/2 inch] HEX SOCKET.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCH]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH	DWN: 09 JAN 2015 CHK: D. MURUGLAH A. BULZA APVD: B. JOHNSON 25 MAY 2016	NAME: SHEARBOLT PIN CONNECTOR, TIN PLATED, 2/0 AWG CU STUD TO 2-4/0 AWG CONDUCTORS
MATERIAL: SEE BOM	FINISH: SEE BOM	PRODUCT SPEC: - APPLICATION SPEC: - WEIGHT: -	SIZE: A2 CAGE CODE: 00779 DRAWING NO: C-2182442

CUSTOMER DRAWING

SCALE: NTS SHEET: OF REV: H