

## Sales Outline Drawing

Revision:

F

## Specifications:

|                       |   |
|-----------------------|---|
| Sound Level Category  | Medium  |
| Mode of Operation     | Slow Double Pulse @ 0.5 PPS   |
| Voltage Rating        | 6 to 16 VDC   |
| Frequency             | 3900 ± 500 Hz   |
| Loudness @ 2 FT       | 75 to 85 dB(A) Typ.   |
| Current Draw          | 40mA MAX  |
| Housing Material      | 6/6 Nylon, Color: Black   |
| Storage Temperature   | -40° to +80° C  |
| Operating Temperature | -30° to +65° C  |
| Panel Mounting        | Recommended hole size is 22.5 mm. Thread front will fit standard 22.5mm hole. |
| Knurled Nut           | Used to attach part to panel. The max recommended torque is 10 in-lbs.        |
| Weight (Typical)      | 28 g  |
| NEMA 3R,4X, & 12      | Approved with use of included gasket.   |
| cUL Recognition       | cUL Recognized  |
| Options               | Please contact factory.   |

## Dimensions: Inches (mm)

## cUL Recognized

PATENT NUMBER 9576442

## ROHS Compliant

