




DIMENSIONS (IN.)					
No. OF PINS	A	B	C	D	E
09	1.626	0.606	0.984	1.268	0.512
15	1.705	0.606	1.312	1.598	0.512
25	1.949	0.606	1.852	2.146	0.512
37	2.138	0.606	2.500	2.783	0.512

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) STRAIN RELIEF CLAMPS
- (2) STRAIN RELIEF SCREWS (M3x0.5mmx6)
- (2) MOUNTING SCREWS (M3x0.5mmx8mm)
- (2) THUMBSCREWS (#4-40)
- (3-SETS) METALIZED PLASTIC INSERTS

SPECIFICATIONS:

- BACKSHELL: DIE CAST ZINC ALLOY
- PLATING: NICKEL
- GROMMET: THERMOPLASTIC ABS
- COLOR: NATURAL NICKEL PLATED
- SCREW: STEEL, ZINC PLATED
- CLAMP: STEEL, NICKEL PLATED
- OPERATING TEMP: -40° C TO +120° C

952-YYY-030R121

SERIES

POSITIONS

009

015

025

037

MATERIAL

030 = DIE CAST (NICKEL)

RoHS COMPLIANT

R = HIGH TEMP. PROCESS

COLOR

12 = METALIZED

PUT-UP

1 = KIT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

DATE:
03/29/2007

UNITS = inches

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET
1 OF
1

REV
3

DWG NO.
952-YYY-030R121