


LOC	DIST	REVISES					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—						
			G2	REVISED PER ECR-14-013846	17SEP2014	NK	DC



端子挿入時(被覆外形3.1の時)
MATING WITH REC CONTACT
(EX. WIRE INSULATION DIA 3.1)

端子型番
REC CONTACT P/N: 170046-2
電線
WIRE: AWG#14 (2mm²)

- 1 APPLICABLE CONTACT P/N 170046-1, -2, -3, 170096-1, -2, 42640-2, 42731-2, 170095-1, 170213-1, -2, -3, 170183-1, -2, 170187-1, -2, 41450, 41829, 61227-1, 63609-1.
- 2 GENERAL TOLERANCE: ± 0.25 .
- 3 NOT APPLICABLE AWG#10 (5mm²) WIRE CRIMPING CONTACT.
- 4 COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT CARRYING CONNECTION DETAILED IN IEC 60335-1. SECTION 30 (GWT).

UL94 V-0, GWT	NATURAL	7-171706-1
UL94V-2 調湿品	自然色	2-171706-1
UL94V-2 MOISTURE ITEM	NATURAL	
タイコエレクトロニクスアンプ韓国製品 Tyco Electronics AMP-KOREA Product	自然色	1-171706-1
UL94V-0	NATURAL	
UL94V-2	赤色	171706-2
UL94V-2	自然色	171706-1
UL94V-2	NATURAL	
備考	色調	型番
REMARKS	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SATO 04DEC2007	TE TE Connectivity	
DIMENSIONS: 単位: 特 mm		CHK S. MANABE 04DEC2007		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD S. MANABE 04DEC2007	NAME 名称	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 製品規格	250 AMP IPD	
MATERIAL 材料 66ナイロン 66NYLON		FINISH 仕上	RESTRICTED TO	
		WEIGHT	SIZE A3	
		CUSTOMER DRAWING	CAGE CODE 00779	
			DRAWING NO C-171706	
			SCALE 尺 1/1	
			SHEET 1 OF 1	
			REV G2	