



THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	,19
(C) COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.			
COMPONENT	MATERIAL	FINISH	
HOUSING CLAMP NUT MOUNTING NUT	STAINLESS STEEL PER ASTM-A-484 OR ASTM-A-582 TYPE 303	GOLD PLATED PER ASTM-B-488 -	
- DIELECTRIC -	PTFE FLUORCARBON PER ASTM-D-1457 -	- - -	
- CENTER CONTACT -	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197 ALLOY C17300, CONDITION H	GOLD PLATED PER ASTM-B-488	
"O" -RING -	BUNA-N PER MIL-P-25732 -	- - -	
- SHRINK TUBING -	HEAT SHRINKABLE POLYOLEFIN COMPOUND PER MIL-I-23053/4	- - -	

LOC	DIST	REVISIONS					
DF	XO	P	LTR	DESCRIPTION	DATE	DWN	APVD
			0	RELEASED	10-01	CT	RG



RECOMMENDED MOUNTING HOLE

		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 10-3-01		 TYCO Electronics Corporation Harrisburg, PA 17105-3608	
DESIGNED TO USE .085 SR CABLE CABLE ENTRY DIAMETER MIN		DIMENSIONS: INCHES (mm)		CHK R.GROSS 10-3-01			
HOUSING: .089				APVD R.GROSS 10-3-01		NAME OSP REAR MOUNT FEED-THRU CABLE PLUG, RF	
CONTACT: .020				PRODUCT SPEC —			
SEE TABLE		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±— 1 PLC ±— 2 PLC ±— 3 PLC ±.005 (0.13) 4 PLC ±— ANGLES ±—		APPLICATION SPEC —		SIZE A2	
MATERIAL		FINISH		WEIGHT —		CAGE CODE 00779	
				CUSTOMER DRAWING		DRAWING NO C- 1218776	
						RESTRICTED TO —	
						SCALE 8:1	
						SHEET 1 of 1	
						REV 0	