



CONTRACT NO. AF33-600-42941

REV	DOCUMENT	CHANGED BY	CHECK
8	206104	GLH 8AUG02	SAV



NOTE:

- 1 - UNIT INCLUDES 6X CAT. LIST. ISM3 TYPE BASIC SWITCHES
- 2 - FOUR MOMENTARY POSITIONS INDICATED BY A, B, C, AND D
- 3 - 3X FLOATING TYPE MTG NUT ARE LOCATED WITHIN ±.020 OF TRUE LOCATION
- 4 - MOVING TOGGLE IN ONE DIRECTION OPERATES SWITCH OR SWITCHES IN OPPOSITE DIRECTION
- 5 - CUP IS WATER TIGHT
- 6 - SCREWS SEALED IN PLACE, SLOTS OF SCREWS FILLED WITH EPOXY



UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:			
	☒ US (inch) CUSTOMARY	☐ SI (mm) METRIC	
NO PLACE	X	±.040	±1
ONE PLACE	.X	±.030	±0.4
TWO PLACE	.XX	±.015	±0.15
THREE PLACE	.XXX	±.005	±
ANGLES		±	±
RAW MATERIAL-COMMERCIAL STANDARD			
THIRD ANGLE PROJECTION			

DRAWN	GLH	08AUG02
CHECK	SAV	08AUG02
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED		
PTC 3D	ASME Y14.5M-1994	

CHARACTERISTICS			
OPERATING FORCE----- 3-5 LB			
ELECTRICAL DATA			
VOLTAGE	RES	IND	MOTOR
30 VDC	5	3	
115 VAC, 400 CYCLE	5	5	4.0

Honeywell			
TITLE SWITCH, , ENCLOSED			
SIZE	DWG TYPE	DRAWING NAME	REV
B	E	4TF2-2	8
SCALE	FULL	WEIGHT 13.0 OZ	SHEET 1 OF 1