

LOC	DIST	REVISIONS					
DF	XO	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	03-0490-02	11-02	JMK	JL

This diagram shows an exploded view of a mechanical assembly. The components are arranged horizontally along a central dashed axis. From left to right, the parts are: a large flange with a central hole, a smaller flange, a long thin shaft with a central hole, a small cylindrical bush, a larger cylindrical bush with a textured surface, a small flange, a larger flange with a central hole, and a long thin shaft with a central hole. The components are shown in a perspective view, with the central axis indicated by a dashed line.

AS SHIPPED TO CUSTOMER

Technical drawing of a cable-to-panel connector assembly, showing side and front views with dimensions and labels.

Side View Dimensions:

- Overall length: 1.125 [28.58] MAX
- Distance from center contact to ferrule: .375 ± .010 [9.53 ± 0.25]
- Ferrule thickness: .065 [1.65]
- Thread specification: .250-36 UNS-2A

Labels:

- CENTER CONTACT
- INNER SLEEVE
- DIELECTRIC
- HOUSING
- FERRULE
- CABLE (CUSTOMER SUPPLIED)
- CLAMP NUT .250 [6.35] HEX

Front View Dimensions:

- Panel hole diameter: Ø.102 [2.59] 4 PLC
- Distance from center to hole center: .340 [8.65] TYP
- Overall panel size: .500 SQ [12.70]

ASSEMBLED VIEW

1052047

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. KAISER	9/11/02
		CHK J. LIPPERT	11-20-02
		APVD J. LIPPERT	11-20-02
DIMENSIONS: INCHES [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 [0.13] 4 PLC ± ± — ANGLES ± —	
MATERIAL	FINISH	PRODUCT SPEC	—
SEE TABLE	SEE TABLE	APPLICATION SPEC	408-4921
		WEIGHT	TBD
		CUSTOMER DRAWING	

tyco <i>Electronics</i>		Tyco Electronics Corporation Harrisburg, PA 17105	
NAME SMA STRAIGHT FLANGE MOUNT CABLE JACK—CRIMP ATTACHMENT (M39012/58—3026) CAT C			
SIZE A2	CAGE CODE 00779	DRAWING NO C-1052047	RESTRICTED TO —
SCALE 5:1		SHEET 1 OF 1	REV B