

PART NO. AND CH. CODE	W ₁ ±0.4	W ₂ ±0.4	H ₁	H ₂	A	B	WIRE SIZE
7116-4052-08.Ⅱ (7B16-4052-08.Ⅱ)	2.30	3.60	(2.19)	(3.19)	3.00	6.20	AVSS 0.3~AVS 0.5 EQUIVALENT
7116-4053-08.Ⅱ (7B16-4053-08.Ⅱ)	3.00	4.50	(2.91)	(3.89)	4.00	7.20	AVS 0.5~AVS 1.25 EQUIVALENT

注記

△ 1. 嵌合相手品番：7114-4052-08 ETC. (7B14-4052-08 ETC.)

△ 2. 材質：C2600 t=0.25

△ 如理：ニッケル下地めっき

△ 金めっき

△ 金フラッシュめっき

△ 編めっき

△ 3. () 内品番は、エアバッグ (A/B) 回路及び別管理回路に使用する時に適用すること。

NOTES

△ 1. MATING PART NO. : 7114-4052-08 ETC.

(7B14-4052-08 ETC.)

△ 2. MATERIAL : C2600 t=0.25

TREATMENT : NICKEL UNDER PLATING

△ GOLD PLATING

GOLD FLASH PLATING

TIN PLATING


△ 3. PART NUMBERS IN PARENTHESIS SHALL

BE USED FOR AIR BAG (A/B) CIRCUITS


AND OTHER CIRCUITS DESIGNATED

FOR SPECIAL MONITORING.



△	01.06.07	CHANGED PART NAME & FORM. Ⅱ	C01-X545	A.T
△	01.01.29	CHANGED PLATING. Ⅱ	C01-X033	E.F
△	98.07.18	CHANGED NOTE & DIMENSION	C97-N454	H.K
△	97.09.12	CHANGED PLATING. Ⅲ	C97-M928	H.K
△	97.07.01	CHANGED FORM. Ⅱ	C97-M318	H.K
△	96.01.19	ADDED A/B PART NO. Ⅱ	C96-L133	M.T
△	93.08.18	CHANGED FORM	C93-L882	H.F
△	92.03.12	CORRECTED AN ERROR IN WRITING	C92-6321	H.K
△	92.03.10	NEW	C92-6279	H.K
LET	DATE	REVISION RECORD	NO.	CHKD
GENERAL TOLERANCE				
10MAX	50MAX	100MAX	250MAX	2500VR
A ±0.15	±0.2	±0.3	±0.5	±0.75
B ±0.2	±0.3	±0.55	±0.95	±1.4
(C) ±0.3	±0.5	±0.8	±1.4	±2
SPECIFIED				
MASS				
g				




SEC. D-D



SEC. C-C





SEC. A-A



△ TIN PLATING AREA

△ GOLD PLATING AREA



SEC. A-A

A 96.01.19		ADDED A/B PART NO. A		C96-L133		M. T		CUSTOMER		MATERIAL SPEC.		SEE NOTES		TREAT. & FIN.		ISSUE MARK	
A 93.08.18		CHANGED FORM		C93-L882		H. F		CUSTOMER PART NO.		CUSTOMER DWG NO.							
A 92.03.12		CORRECTED AN ERROR IN WRITING		C92-6321		H. K											
92.03.10		NEW		C92-6279		H. K		OFFICE		TRIAL PART NO.							
LET		DATE		REVISION RECORD		NO.		CHKD		VENDOR							
				GENERAL TOLERANCE				VENDOR NO.									
		10MAX		50MAX		100MAX		250MAX		250OVR		ANGLE		ECCENT			
A		±0.15		±0.2		±0.3		±0.5		±0.75		±30'		0.1			
B		±0.2		±0.3		±0.55		±0.95		±1.4		±30'		0.1			
C		±0.3		±0.5		±0.8		±1.4		±2		±30'		0.15			
SPECIFIED												MASS		g			
												加 藤 川 梨		101.06.14		01.05.12	
												A. MAEDA		OHKUBO		90.10.18	
												12		杉山 じ		01.06.07	
												5/1		3			
												m		m			
												92.03.03		12.03.03			
												R					
												APPROVED		CHECKED			
												</					