

Han 24B Prot.Cover w latch Plastic black



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 724 5401
Specification	Han 24B Prot.Cover w latch Plastic black
HARTING eCatalogue	https://b2b.harting.com/09307245401

Identification

Category	Accessories
Series of hoods/housings	Han® B
Type of accessory	Protection cover
Description of the accessory	for hoods Thermoplastic With board locks

Version

Size	24 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	34 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140048850
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors