




DIALIGHT PART NUMBER	LENS COLOR	PEAK EMISSION WAVELENGTH (nm) TYP	DOMINANT WAVELENGTH (nm) TYP	VIEWING ANGLE (°) 2 Θ 1/2	CAPACITANCE (pF) @ V _F =0; f = 1 MHz	LUMINOUS INTENSITY (mcd) @ I _F =20mA; 25°C		FORWARD VOLTAGE (V) @ I _F =20mA; 25°C		REVERSE CURRENT (μA); 25°C
					TYP	MIN	TYP	MIN	TYP	MAX
521-9636F	RED DIFF.	660	638	60	30	19	60	1.8	2.4	100 @ V _R =4V
521-9637F	RED TRANS.	660	638	45	30	40	135	1.8	2.4	100 @ V _R =4V
521-9638F	GREEN TRANS.	565	569	45	35	19	70	2.1	2.6	100 @ V _R =5V

REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	—	NEW RELEASE	KLJ	7.8	10	5-15-08

RoHS COMPLIANT 521-963XF
 Part Numbers with the "F" suffix ending are RoHS Compliant.
 Packaging is marked with "RoHS Compliant" label or equivalent
 markings. Parts can be wave soldered, dip soldered or hand
 soldered using typical lead-free soldering process with max
 260°C temp. for 5 sec.



- NOTES:
1. DIE: AlGaAs FOR RED
GaP FOR GREEN
 2. LEADS: 30.0μm-50.0μm TIN (Sn) OVER 20.0μm
NICKEL (Ni) ON COPPER (Cu).
 3. SOLDER ADHERANCE: BOTH LEADS PER MIL-STD-202E, METHOD 208C.
 4. PIN NUMBERS FOR REFERENCE ONLY; DESIGNATION NON-EXISTENT ON PART.
 5. LEAD SPACING MEASURED NEAR EPOXY PACKAGE.
 6. BULK PACKAGING.
 7. DIALIGHT PART NUMBERS: 521-9636F, 521-9637F, 521-9638F
 8. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING, AND STORAGE IN ACCORDANCE WITH IPC-A-610.



ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT	RED DIFFUSED	RED TRANSPARENT	GREEN TRANSPARENT	UNITS
POWER DISSIPATION	100	100	100	mW
CONTINUOUS FORWARD CURRENT	40	40	30	mA
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 0.1 ms PULSE WIDTH)	200	200	120	mA
DERATING LINEAR FROM 50°C	0.5	0.5	0.4	mA/°C
REVERSE VOLTAGE	4		5	V
SOLDERING TEMPERATURE (.063" FROM BODY)	260 FOR 5 SEC			°C
OPERATING TEMPERATURE	-40 TO +100		-55 TO +100	°C
STORAGE TEMPERATURE	-55 TO +100			°C



ATTENTION:
 OBSERVE PRECAUTIONS FOR
 HANDLING ELECTROSTATIC
 SENSITIVE DEVICES

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.		
SCALE: 6.000	DRAWING NUMBER	REV
ALL DIM'S IN: INCHES (MM)	C-17614	A
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE	
FRACTIONS: ±1/64	3mm LED	
DECIMALS (.XX): ±.02	RoHS COMPLIANT	
DECIMALS (.XXX): ±.010	MATERIAL	
DECIMALS (.XXXX): ±.0005		
ANGLES: ±1°		
FINISH:		
FSCM 83330	Dialight	1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727
	SHEET 1 OF 1	FAMILY TABLE: