



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
FT	0		B2	OBSOLETING PART NUMBERS 15 POSITION AND ABOVE		27MAR2015	CR PS

MATERIAL:
HOUSING: THERMOPLASTIC PA, UL94V-0, BLACK.
TERMINALS: BRIGHT TIN PLATED, COPPER ALLOY.
SCREWS: 6-32, STEEL, ZINC PLATED W/ CLEAR CHROMATE.

ELECTRICAL:
UL CLASS C: 20A, 150V.
UL CLASS D: 10A, 300V.
CSA TYPE B: 20A, 300V.
CSA TYPE C: 20A, 300V.
CSA TYPE D: 10A, 300V.
CSA TYPE E: 20A, 300V.
WIRE RANGE: 12-22 AWG.


MECHANICAL:
OPERATING TEMP.: -40° TO +105°C.
RECOMMENDED TIGHTENING TORQUE: 7 IN-LBS.

- ① SCREWS BOTTOMED.
- ② PRELIMINARY PART NUMBER.
- ③ OBSOLETE PARTS.



RECOMMENDED PCB LAYOUT

③	OBSOLETE	SEE NOTE	9.425	9.815	28	4DB-P208-28	2-1546460-8
③	OBSOLETE	SEE NOTE	9.100	9.490	27	4DB-P208-27	2-1546460-7
③	OBSOLETE	SEE NOTE	8.775	9.165	26	4DB-P208-26	2-1546460-6
③	OBSOLETE	SEE NOTE	8.450	8.840	25	4DB-P208-25	2-1546460-5
③	OBSOLETE	SEE NOTE	8.125	8.515	24	4DB-P208-24	2-1546460-4
③	OBSOLETE	SEE NOTE	7.800	8.190	23	4DB-P208-23	2-1546460-3
①③	OBSOLETE	SEE NOTE	7.475	7.865	22	4DB-P208-22-092	2-796988-0
③	OBSOLETE	SEE NOTE	7.150	7.865	22	4DB-P208-22	6-1437667-2
③	OBSOLETE	SEE NOTE	6.825	7.540	21	4DB-P208-21	2-1546460-1
③	OBSOLETE	SEE NOTE	6.825	7.215	20	4DB-P208-20	2-1546460-0
③	OBSOLETE	SEE NOTE	6.500	6.890	19	4DB-P208-19	1-1546460-9
③	OBSOLETE	SEE NOTE	6.175	6.565	18	4DB-P208-18	1-1546460-8
③	OBSOLETE	SEE NOTE	5.850	6.240	17	4DB-P208-17	1-1546460-7
③	OBSOLETE	SEE NOTE	5.525	5.915	16	4DB-P208-16	1-1546460-6
③	OBSOLETE	SEE NOTE	5.200	5.590	15	4DB-P208-15	1-1546460-5
			4.875	5.265	14	4DB-P208-14	1-1546460-4
			4.550	4.940	13	4DB-P208-13	1-1546460-3
			4.225	4.615	12	4DB-P208-12	1-1546460-2
			3.900	4.290	11	4DB-P208-11	1-1546460-1
			3.575	3.965	10	4DB-P208-10	1-1546460-0
			3.250	3.640	9	4DB-P208-09	1546460-9
			2.925	3.315	8	4DB-P208-08	796658-5
			2.600	2.990	7	4DB-P208-07	796658-5
			2.275	2.665	6	4DB-P208-06	796658-4
			1.950	2.340	5	4DB-P208-05	1546460-5
			1.625	2.015	4	4DB-P208-04	6-1437667-1
			1.300	1.690	3	4DB-P208-03	1546460-3
			.975	1.365	2	4DB-P208-02	6-1437667-0
COMMENTS			DIM B	DIM A	NO. OF POS.	CATALOG NUMBER	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 10/3/03		 TE Connectivity									
		CHK S YODER 10/3/03											
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME									
		APVD S YODER 10/3/03		4DB SERIES P208 STYLE —									
		PRODUCT SPEC —											
		APPLICATION SPEC —											
		MATERIAL —		FINISH —		SIZE A3		CAGE CODE 00779		DRAWING NO C-6-1437667-0		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE NTS		SHEET 1 OF 1		REV B2					