









P.C.B. LAYOUT



CIRCUIT: SPST ▲



▲
ACTUATOR
COLOR: BLACK



▲
GOLD DOME:
(P990005)

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: GOLD
5. RATING: 50mA, @ 12VDC
- ▲ 6. OPERATING FORCE: 160 ± 50gf
7. TRAVEL: 0.25mm ± 0.1mm
8. CONTACT RESISTANCE: 100 mΩ MAX. (INITIAL)
9. ELECTRICAL LIFE: 100,000 CYCLES MIN.
10. ▲ DENOTES CRITICAL PARAMETER
11. OPERATING TEMP: -40°C TO 85°C

G	24752	BLACK ACTUATOR	2/19/21	JM
F	24550	REMOVE STEP IN HOUSING, CHANGE TEMP	10/19/20	JM
E	22831	UPDATE DRAWING	5/2/17	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE TL1105XF160R

SCALE 4:1

DATE 1/3/2012

DR BGL

DWG P020229

REV G