






▲ ILLUMINATED
COLOR: RED / BLUE



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: x.x = ± 0.4 mm
x.xx = ± 0.25 mm
3. RATING: DC 30V, 0.3A
4. OPERATING FORCE: 200 ± 100 gf
5. TRAVEL: 3.3mm FULL TRAVEL
6. LIFE CYCLES: 10,000 CYCLES
7. OPERATING TEMPERATURE: -20°C to 70°C
8. CONTACT RESISTANCE: 20m Ω MAX.
9. INSULATION RESISTANCE: 100M Ω MIN@ 500VDC
- ▲ 10. LED COLOR: RED / BLUE
11. ▲ DENOTES CRITICAL PARAMETER.

LED SPECS	UNITS	RED	BLUE
FORWARD CURRENT	mA	20	20
FORWARD VOLTAGE @ 20mA	V	1.8 Typ - 2.6 Max	2.7 Typ - 3.5 Max
LUMINOUS INTENSITY @ 20mA	MCD	200 typ.	400 typ.

REV	ECO NO	DESCRIPTION	DATE	BY
A	ECO-100036	Release	04/22/21	MW

				OBJECT ID 100115954
TITLE WBL2UOARBQ				
SCALE 2:1	DATE 4/20/2021	DR MW	DWG B400021	REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED