









REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		图框升级整理图面	2024.08.13	阿 树



- SPECIFICATIONS
- Voltage rating:125V AC/DC
 - Current rating:1A AC/DC
 - Withstanding Voltage:500V AC/minute
 - Temperature range:-45°C~+125°C
 - Insulation resistance:≥100MΩ
 - Contact resistance:≤20mΩ

PART NO.:
X9821 W R S-XX-LP SN
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
② Category:W-Wafer
③ Welding Board Angle:R-Stright 90°
④ Welding Way:S-SMT
⑤ Row No-Pin No: XX-02P~16P
⑥ Material:LP-LCP UL94V-0
⑦ Planting Category:SN-Bright Tin Plating



Poles	Dimension mm				Poles	Dimension mm			
	A	B	C	D		A	B	C	D
2	1.25	4.25	7.75	3.20	10	11.25	14.25	17.75	13.20
3	2.50	5.50	9.00	4.45	11	12.50	15.50	19.00	14.45
4	3.75	6.75	10.25	5.70	12	13.75	16.75	20.25	15.70
5	5.00	8.00	11.50	6.95	13	15.00	18.00	21.50	16.95
6	6.25	9.25	12.75	8.20	14	16.25	19.25	22.75	18.20
7	7.50	10.50	14.00	9.45	15	17.50	20.50	24.00	19.45
8	8.75	11.75	15.25	10.70	16	18.75	21.75	25.25	20.70
9	10.00	13.00	16.50	11.95					

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

DESIGN	阿 树	VIEW:	MODEL TYPE: 1.25 mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X9821WRS-XX-LPSN
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1