

HONEYWELL
PART NUMBER

77344

REV	DOCUMENT	CHANGED BY	CHECK
B	0068753	VKK 03SEP10	CMH

CUSTOMER: _____

APPROVED BY: _____

DATE: _____



CUSTOMER
PART NO.: _____HONEYWELL PART NUMBER, N.O., VACUUM
SETTING AND DATE CODE

2X 1/4 BLADE TERMINAL

(.4375) HEX.

1/8-27 NPT

(2.3)



NOTES:

1. SINGLE CIRCUIT NORMALLY OPEN VACUUM SWITCH.
2. CLOSING ADJUSTMENT RANGE 1.1 – 22 IN. Hg.
3. DIMENSIONS ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.


CUSTOMER PRINT

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACES	X	±	—
ONE PLACE	.X	±	.020
TWO PLACE	.XX	±	.010
THREE PLACE	.XXX	±	.005
FOUR PLACE	.XXXX	±	.0005
ANGLES	X	±	0°30'

THIRD ANGLE PROJECTION



DRAWN

D MCGEE

24OCT01

CHECK

—

—

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

AUTOCAD

2D

Honeywell

TITLE

VACUUM SWITCH N.C.
SCREW TERMINALS
5000 SERIES SWITCH

SIZE

A

TYPE

I

CAGE CODE

—

DRAWING NAME

77344

REV

B

SCALE

NONE

SHEET

1 OF 1