

**Sales Outline Drawing**

**May not be suitable for all medical and aerospace applications.**

**Specifications: Contact Mallory Sonalert to discuss your application.**

Resonant Frequency (Hz)	2900 $\pm$ 500
Operating Voltage (Vp-p/max)	30
Rated Voltage (Vp-p)	5.0
Current Consumption (mA/max)	5.0 at Rated Voltage
Sound Pressure Level (dB/min)	95 at 10cm at Rated voltage
Capacitance (pF)	30,000 $\pm$ 30% at 120 Hz
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 757 UL94HB plastic resin (Color: Black)
Lead Wires	28 AWG (Red + Black)
Weight (Grams)	11.2
Options	For other options contact factory

**NO CIRCUITRY**

**Dimensions:** (units: mm)

**ROHS Compliant**

