

DRAWING FOR REFERENCE: This is subject to change without notice
08/11/2012

TO
RF

1			2			3			4		
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		
△				..	△				..		
△					△				..		
△					△				..		

A

APPLICABLE OUTER CONDUCTOR CRIMPING TOOL : UM.MSS-T-1(1.5HOLE)

B

C

D

E

F

15.5±0.6

□5.7±0.2

3.5±0.15

22.8±0.5

11.5±0.1

5

6

2

7

ATTACHED

BRAZING

3

8

4

5

1

PRESS FITTING

PRESS FITTING

PRESS FITTING

4	PHOSPHOR BRONZE	GOLD PLATING	8	BERYLLIUM COPPER	NICKEL PLATING
3	PTFE		7	COPPER	GOLD PLATING
2	BRASS	GOLD PLATING	6	BRASS	GOLD PLATING
1	BRASS	GOLD PLATING	5	PHOSPHOR BRONZE	GOLD PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
RoHS COMPLIANT		<i>Y. Sugiyama</i> 06.03.13	<i>T. Katayama</i> 06.03.14	<i>H. Shimizu</i> 06.03.15	<i>J. Mitani</i> 06.03.15	

	DRAWING NO.	PART NO.
	EDC4-029951-40	PO51-LP-1.5-A(40)
SACLE 5 : 1		CODE NO.
UNITS mm		CL330-0007-6-40

1	2	3	4
---	---	---	---

FORM NO.228