

HOME > Product Info

Product Category

Product Info

1 Products

	1-1	
Product No.	PO51-LP-1.5W-1A(40)	
HRS No.	330-0200-6 40	
Status	In Production	
RoHS	Yes	
Series	PO51	
Category	Coaxial Connectors	
No. of Positions	N/A	
Contact Mating Area Plating	Gold	
Contact Gender	Male	
Connector Type	Cable	
PCB Mount Type	N/A	
Current Rating(Amps)(Max.)	N/A	
Impedance (ohm)	50	
Frequency (GHz)(Min)	0	
Frequency (GHz)(Max)	1	
V.S.W.R. (Max)	1.2	
Termination Style	Soldering	
Temperature (deg C)	-55 to 85	
Mating/Unmating Cycles	500	
Applicable Cable	1.5DQEW	
Generic Name	N/A	
Selling Unit	1pcs.(1pcs.)	
General Description	Plug; Right angle; Pushpull lock	
Inquiry	REQUEST	
Similar Products	N/A	
e-Commerce	E-Commerce ▶	
Product No.	PO51-LP-1.5W-1A(40)	
HRS No.	330-0200-6 40	
	1-1	

[▶ Terms of Service](#)
[▶ RoHS](#)