

# PRODUCT NUMBER

10129149-101-XXXLF

## PLATING


1 = 0.76µm GOLD/GXT  
ON CONTACT AREA  
UNDERPLATING  
1.27µm Ni MIN

RoHS COMPLIANT


PACKAGING, NOTE 3

TOTAL NB OF POSITIONS  
02 TO 25

PIN STYLE




TRANSITION AREA  
1.27µm Ni MIN



## NOTES:

- HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK
- PIN MATERIAL : PHOSPHOR BRONZE
- PACKAGING:  
= STANDARD PACKAGING IN BLIBOX  
K = TAPE & REEL WITHOUT PICK UP CAP AS AVAILABLE  
U = TUBE WITHOUT PICK UP CAP
- 9N MIN RETENTION IN EITHER DIRECTION
- TO DETERMINE DIMENSIONS :  
N = NUMBER OF POSITIONS PER ROW  
EXAMPLE : 12 POS  $N \times 2.54 = 30.48\text{MM}$



mat'l. code				surface	tolerance	projection	product family	
				ISO 1302	ISO 406	ISO 1101	HEADER BSTIK	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
A		BVE	15.04.08	angles	linear	.X $\pm 0.3$	HDR SINGLE ROW	
B	F-28512	LMU	17.02.06			.XX $\pm 0.13$	-U- BENDING	
C	F-28643	DDE	17.11.30	$\pm 2'$		.XXX $\pm 0.05$	scale 7:1	
				dr	L.MULIN	14.02.17	dwg no	
				engr	J.COMPAGNON	14.02.18	sheet 1 of 1	
				chr			size	
				appo			10129149	
				sheet index	revision sheet		type	
							CUSTOMER Drawing	