




REVISIONS					
ZONE	LTR	ECN	DESCRIPTION	DATE	APPROVED
	P	28902	REVISED & REDRAWN ORIG. RELEASE BY B.T. 6-23-85	8/13/84	kg
	R	39342	UPDATE REV. LETTER	9/12/84	kg

R1 LOAD CORRECT DRAWING



TYCO CUSTOMER DWG 1466288

NOTES: UNLESS OTHERWISE SPECIFIED:

1. THIS CONN. MATES WITH ALL PLUGS IN SERIES J-50 AS LISTED IN MICRODOT CATALOG.
2. SILVER PLATE .0002" MIN. PER QQ-S-365 TYPE II, GRADE A.
3. GOLD PLATE PER MIL-G-45204 TYPE II, GRADE C, CLASS I.
4. WORKING VOLTAGE - 750 V.R.M.S.
5. INSULATION RESISTANCE - 15×10^9 OHMS MIN.
6. PANEL THICKNESS: .160 MAX.

1		003-0268-0001	GASKET	SILICONE RUBBER PER ZZ-R-765, RED	7
	1	003-0268-0000	GASKET	SILICONE RUBBER PER ZZ-R-765, BLK	6
1	1	003-0306-0001	SHAKEPROOF LUG	# 425 BRONZE ALLOY	5
1	1	003-0009-0001	HEX NUT	BRASS PER QQ-B-626	4
1	1	003-1315-0002	SOCKET CONTACT	BERYLLIUM COPPER QQ-C-530	3
1	1	003-1316-0001	INSULATOR	TELFON PER L-P-403	2
1	1	003-1317-0001	HOUSING	BRASS PER QQ-B-626	1
2	1		PART NUMBERS	DESCRIPTIONS	MAT'L & SPECIFICATIONS
*	No				ITEM NOS.

PARTS LIST

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
FRACTIONS DECIMALS ANGLES
± .XX ± .XXX ± .010 ± 2°

MATERIAL

NOTED

FINISH

NOTED

NEXT ASSY USED ON

APPLICATION

DO NOT SCALE DRAWING

CONTRACT NO.

APPROVALS

DATE

DRAWN C. TIONGCO

7-27-84

CHECKED

PR. ENG. kg

8/9/84

APPD.



MALCO
A MICRODOT COMPANY, INC.
220 PASADENA AVE., SO. PASADENA, CALIF. 91030

PROD.
CODE
731

CODE
COM

SIZE CODE IDENT NO. DRAWING NO.

C

98278

031-0050-000*

SCALE ~

SHEET 1 OF 1