




GENERAL TOLERANCE									
10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE
A	±0.15	±0.2	±0.3	±0.5	±0.75		±0.2	±0.3	±3°
B	±0.2	±0.3	±0.55	±0.95	±1.4		±0.5	±2.5	0.1
C	±0.3	±0.5	±0.8	±1.4	±2				±3°
									0.15

PART NO. AND CH. CODE	COLOR
7183-4347	NATURAL
7183-4347-30	BLACK



注 記

- △ 1. かん合相手品番 : 7183-4347:A (直結専用)
2. 適用端子品番 : 7116-4114-02 (CAVS 0.3~0.5)
: 7116-4115-02 (CAVS 0.85~1.25)
: 7116-4116-02 (AVSS 2~AVS 3)

NOTES

- △ 1. MATING PART NO. : 7183-4347 : A (DIRECT)
2. APPLICABLE TERMINAL NO. : 7116-4114-02 (CAVS 0.3~0.5)
: 7116-4115-02 (CAVS 0.85~1.25)
: 7116-4116-02 (AVSS 2~AVS 3)

GENERAL TOLERANCE									
10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	ANGLE	ECCENT			
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	O.1		
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	O.1		
C	±0.3	±0.5	±0.8	±1.4	±2	0-15			

GENERAL TOLERANCE			CUSTOMER		CUSTOMER DWG NO.		MATERIAL SPEC.	
Δ	11/01/11	ADDED COLOR PART NO. ETC.	C11-2015	K. I	CUSTOMER PART NO.		Δ PBT (COLOR SEE TABLE)	TREAT. & FIN.
Δ	10/10/15	CHANGED PART NAME	C10-ZA78	M. A				
Δ	02/11/05	NEW	C02-Y324	K. Y	OFFICE	TRIAL PART NO.		
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR			
					VENDOR NO.			
Δ 110 4P HOUSING FEMALE								

SPECIFIED					MASS						PART NO.		CH. CODE		SET DWG NO.	
10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	7183-4347 ETC.	7183-4347:R	7183-4347:R	SET DWG NO.
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	R	NEW	02/11/05	mm	2:1	3				
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN					
C	±0.3	±0.5	±0.8	±1.4	±2	0-15	H. KONDO	K. SUZUKI	K. IKEYA	K. YOSHIDA	E. ITALIA					
							11/01/11	11/01/11	11/01/11	01/09/04	11/01/11	YAZAKI CORPORATION				

YAZAKI CORPORATION

7183-4347:R

7183-4347 ETC.

110 4P HOUSING FEMALE

PBT (COLOR: SEE TABLE)

TREAT. & FIN.

ISSUE MARK