




技术要求:

1. 特性阻抗 $50\ \Omega$
2. 频率范围 0-6GHz
3. 接触电阻 内导体 $\leq 3\text{m}\ \Omega$
外导体 $\leq 2\text{m}\ \Omega$
4. 绝缘电阻 $\geq 5000\text{M}\ \Omega$
5. 盐雾时间 24H
6. 分离力 $\geq 0.28\text{N}$
7. 温度范围 -55°C TO $+155^\circ\text{C}$

公差Tolerance	± 0.05	± 0.1	± 0.2	± 0.3	± 0.5	± 0.05	$\pm 0.5^\circ$
尺寸范围	0-10	10-20	20-50	50-100	>100	D<20	0-180°
Dimension	线型/Linear					孔Hole	角度Angle
Range	未注尺寸公差/Tolerance unless specified						



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2^\circ$ X.X' $\pm 0.5^\circ$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: SMA 带孔90° DIP L17.0	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW17-SMAW1300-1700B	MOLD NO.
	APPROVED BY: 柯南	DATE : 2014-02-23	DRAW NO: HYC-180521430	SHEET NO. 1 OF 1
	SCALE:1:1	SIZE: A4		