

**Mallory Sonalert Products, Inc.**

Part #:

SBT12PHFL**Sales Outline Drawing**


Revision:

C**Specifications:****cUL Recognized to IEC60601-1-8 AMD1
Artificial Perfusion Melody - High Priority Only**

Sound Level Category:	Loud
Mode of Operation:	High Priority Alarm - 10 beeps repeating every 2.5 sec
Voltage Rating:	9 to 12 VDC
Frequency:	150 to 4000 Hz
Loudness @ 10cm:	85 to 95 dB(A) Typ.
Average Current Draw:	<25mA Typ.
Ipk Current*:	75mA
Housing Material:	ABS 777D Plastic Resin, Black
Storage Temperature:	-40° to +85° C
Operating Temperature:	-30° to +65° C
Weight Typical:	0.6 oz (17g)
Options:	Please contact factory.

Dimensions: Inches (mm)**cUL Recognized****ROHS Compliant**

PATENT NUMBER: 7880593



*Ipk = Instantaneous Peak

tolerances: $\pm 0.01 [\pm 0.3]$
 $\pm 0.005 [\pm 0.1]$