






▲ CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. RATING: 12VDC @ 50mA
4. CONTACT RESISTANCE: 100m Ω MAX.
5. INSULATION RESISTANCE: 1000m Ω MIN @ 100VDC
- ▲ 6. OPERATING FORCE: 200 $\pm$ 80gf
7. TRAVEL: 0.45 $\pm$ 0.15mm
8. OPERATING TEMPERATURE: -40°C to 85°C
9. OPERATING LIFE: 500,000 CYCLES
- ▲ 10. LED COLOR: WHITE
11. IP67 RATED
12. ▲ DENOTES CRITICAL PARAMETERS



▲ LED Specifications

LED Color	Forward Current (mA)	Forward Voltage (V @ 20mA)	Luminous Intensity (mcd)
WHITE	20	3.3 typ	450 typ



E-SWITCH®

A	24123	Release	12/11/19	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL6215VF200WBT

SCALE 4:1	DATE 12/10/2019	DR MW	DWG B200633	REV A
--------------	--------------------	----------	----------------	----------