





SCHEMATIC (NON-SHORTING)



P.C.B LAYOUT
BOTTOM VIEW



		—				—
		—				—
		—				—
④	Terminal	—	3	Brass (0.30t)	ag Plated	—
③	Base	—	1	Phenolic Resin		—
②	Cover	—	1	Sus	Natural	—
①	Keystake	—	1	Pa66	Black	—
ITEM	PAPT NAME	TER,NO	QTY	MATERIAL	FINISHING	REMARK

RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100mΩ MAX
TRAVEL	2mm
OPERATING FORCE	250±100gf
OPERATING LIFE(CYCLES)	10,000

广东星坤科技股份有限公司	
法 製	日期
文件工程草	

				ANGLAR	±5°
				L ≤ 4	±0.2
				4 < L ≤ 16	±0.3
				16 < L ≤ 63	±0.4
ON		DATE	REVISED	APPROVED	L > 63 ±0.5
REVISIONS					UNSPECIFIED TOLERANCES



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	SLIDE SWITCH
CHKD		UNIT: mm/in	PART NO.: SS12D07
APPD		SIZE: A4	DWG NO.:
		WEIGHT	SHEET
		REVISIO	