



CONTACT CONFIGURATION  
TIMING (BBM) NON-SHORTING



## NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: GOLD
5. CONTACT RATING: 150mA, 250VAC/DC  
350mA, 110VAC/DC
6. OPERATING FORCE:  $800 \pm 300$  g-cm
7. OPERATING TEMP: -30°C to 85°C
- ▲ 8. CIRCUIT SP: 12 POSITION 30° INDEX (NO STOPS)
9. DIELECTRIC STRENGTH: 1000V RMS MIN.@ SEA LEVEL
- ▲ 10. HARDWARE SUPPLIED ON SWITCH:  
LOCKWASHER and HEX NUT
11. ▲ DENOTES CRITICAL PARAMETER.

| REV                                                                                                          | ECO NO     | DESCRIPTION                       | DATE     | BY | E-SWITCH®            |               |       |             | OBJECT ID |
|--------------------------------------------------------------------------------------------------------------|------------|-----------------------------------|----------|----|----------------------|---------------|-------|-------------|-----------|
| B                                                                                                            | ECO-101041 | update print, added No Stops note | 06/09/22 | MW |                      |               |       |             | 100121705 |
|                                                                                                              |            |                                   |          |    | TITLE KC10A13.001NLF |               |       |             |           |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED |            |                                   |          |    | SCALE 3:2            | DATE 4/6/2022 | DR JS | DWG G527974 | REV B     |