




YAZAKI PART NO.	COLOR
7122-1460	NATURAL
7122-1460-30	BLACK
7122-1460-40	GRAY
7122-1460-50	ORANGE
7122-1460-60	GREEN
7122-1460-70	YELLOW
7122-1460-80	BROWN
7122-1460-90	BLUE

NOTES

- 1)MATING PART NO. :7123-1460 ETC.
- 2)APPLICABLE TERMINAL NO. :7114-1170
:7114-1171

注記

- 1)嵌合相手品番:7123-1460 ETC.
- 2)適用端子品番:7114-1170, 7114-1171

LET	DATE	REVISION RECORD	NO.	CHKD
	88.09.22	NEW	BMC-3105	T.M

GENERAL TOLERANCE									
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT		
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1		
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1		
◎	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15		
SPECIFIED					WEIGHT				

CUSTOMER				MATL.		TREAT.		ISSUE MARK	
CUSTOMER PART NO.		CUSTOMER DWG NO.		SPEC.		NYLON		& FIN.	
OFFICE		STD LIB NO.		NAME		6P 090 MALE HOUSING			
VENDOR									
VENDOR NO.									
DWG TYPE		DWG SOURCE		DWG DATE		UNIT		SCL	
R		NEW		88.09.09		mm		5/1	
APPROVED		CHECKED		CHECKED		DESIGN		DRAWN	
加藤 前島		KANeko		S. YAGI		DWG NO.		7122-1460-R	
88.09.27		88.09.23		88.09.27		88.09.09		TRIAL PART NO.	
YAZAKI CORPORATION									