


Recommended PCB Layout
General Tolerance:±0.05

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃-+85℃

温度范围: -25℃-+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

After environmental testing:≤30mΩ

环境测试后: ≤30兆欧

X9555 W R X-2xXX X-6T V01 XX

① ②③④ ⑤ ⑥⑦ ⑧ ⑨

1. Series No

2. Category:W-wafer

3. Welding Board Angle:R-Right Angle 90°

4. Welding Way:Blank-DIP

5. Row No-Pin No:2xXX-2x02P~2x32P

6. Plug the Pin&Special No:

7. Material:6T-PA6T 94V-0

8. Planting Category:V01-All Gold Flash

V05-All 5u" Gold

9. Color:Blank-Natural Color

poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B
2x02	2.54	12.68	2x12	27.94	38.25
2x03	5.08	15.22	2x13	30.50	40.65
2x04	7.62	17.76	2x15	35.56	45.80
2x05	10.16	20.30	2x17	40.64	50.78
2x06	12.70	22.84	2x20	48.26	58.40
2x07	15.24	25.38	2x25	60.86	71.10
2x08	17.78	27.92	2x30	73.70	84.15
2x09	20.32	30.46	2x32	78.74	89.00
2x10	22.86	33.00			

X9555WR-2xXX-6TV 05	PA6T UL 94V-0	Brass	5u"Gold	X9555H
X9555WR-2xXX-6TV 01			Gold-Flash	
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: Wire to board connector		
DWN		VIEW:	PART NO.: 2.54mm Crimp Style Connectors		
CHKD		UNIT: mm/in	DWG NO.: X9555WR-2xXX-6TV01		
APPD		SIZE: A4	WEIGHT	SHEET 1/1	REVISIT A0

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

广东星坤科技股份有限公司

日期

文件工程章

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn