

1

2

3






YAZAKI PART NO.	W ₁	W ₂	△R ₁	△R ₂	WIRE SIZE
7116-1180	2.10	3.70	0.30	0.95	AVS 0.2~0.5
△(7B16-1180)					EQUIVALENT
7116-1181	3.70	4.20	0.70	1.30	AVS 0.85~1.25
△(7B16-1181)					EQUIVALENT

注記

△ 1. () 内品番は、A/B回路及び特別管理回路に使用する時に適用すること。

NOTE

△ 1. () PART NO. IS USED FOR PARTS ASSOCIATED WITH A/B CIRCUITS OR OTHER SPECIFIED CIRCUIT.



ISSUE MARK

△ 97.02.19	ADDED A/B PART NO.	C97-L247	H. K	CUSTOMER		MATL.	BRASS (t=0.25)	TREAT.	
△ 89.02.21	CHANGED NOTE	C89-6278	K. M	CUSTOMER PART NO.		SPEC.	(TIN PLATING)	& FIN.	
△ 86.04.30	CHANGED FORM & RENEW	C86-5493	T. M			NAME	090 TERMINAL FEMALE		
85.02.26	NEW	C85-5204	T. Y	OFFICE		TRIAL PART NO.			
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR				
GENERAL TOLERANCE				VENDOR NO.					
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED
©	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15		CHECKED
SPECIFIED				MASS				DESIGN	DRAWN
								KANEKO	AKIMOTO
								81.07.31	97.02.19
								YAZAKI CORPORATION	

1

2

3