





REV.	DATE	DESCRIPTION
NC	D1/29/01	INITIAL RELEASE
A	05/01/04	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .118"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex				
8						DRAWN	G.R.S.	05/01/04	PART DESCRIPTION SMA CRIMP PLUG (FOR BELDEN 9913, 9914, LMR-400)			
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.3 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED						
6						ISSUED						
5					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	SHEET	1 OF 1		PART NO. 132298			
4	FERRULE	COPPER	GOLD	1								
3	CONTACT PIN	BRASS	GOLD	1					DWG. NO. 132298.DWG			
2	INSULATOR	TEFLON	NATURAL	1								
1	HOUSING/BODY	BRASS	GOLD	1					REV. A	SIZE A	SCALE NA	
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/132/132298.DWG					