





REV. 0

DCO 143490

COIL: @ 25°C
 RESISTANCE 880 OHMS ±10%
 NOMINAL VOLTAGE 18.0 VDC
 MUST OPERATE 10.5 VDC
 MUST RELEASE 6.0 VDC MAX, 0.91 VDC MIN.


ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX.
 RELEASE TIME 1.5 MS MAX.

CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 14MAR02

CK 15MAR02

CIL Technologies
 advanced control electronic solutions

CUST. OPL
 CUST. NO. M39016/9-061P REV.

"JMA" RELAY

JMAC-18XP