



PANEL CUTOUT  
MAX. PANEL THICKNESS  
10.0mm [.43]






| SWITCH FUNCTION |          |          |
|-----------------|----------|----------|
| POS. 1          | POS. 2   | POS. 3   |
|                 |          |          |
| ON              | ON       | ON       |
| 1-3, 4-5        | 1-3, 4-6 | 1-2, 4-6 |



## NOTE:

- ALL DIMENSIONS IN mm [INCH]
- GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- RATING: 2A 24VDC
- ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES  
AT FULL LOAD.
- INSULATION RESISTANCE: 1,000 M $\Omega$  MIN.
- DIELECTRIC STRENGTH: 1,500 VAC MIN. FOR 1 MINUTE
- CONTACT RESISTANCE: 50m $\Omega$  MAX. @ 1A 12VDC
- OPERATING TEMP.: -20°C to 55°C
- ▲ DENOTES CRITICAL PARAMETER.
- LAMP VOLTAGE: 12V
- INGRESS PROTECTION: IP65
- HARDWARE SUPPLIED: O-RING AND HEXNUT



| REV | ECO NO     | DESCRIPTION                       | DATE     | BY | E-SWITCH®             |           |     |                   | OBJECT ID |
|-----|------------|-----------------------------------|----------|----|-----------------------|-----------|-----|-------------------|-----------|
| B   | ECO-102081 | ACTUATOR DIMS CHANGE TO REFERENCE | 07/13/23 | JS | TITLE PVK4S22C0SS-A34 |           |     |                   | 100122422 |
|     |            |                                   |          |    | SCALE                 | DATE      | DR  | DWG               | REV       |
|     |            |                                   |          |    | 1:1                   | 7/26/2022 | MJR | 52-PVK4S22C0SSA34 | B         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED