








NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 150mA @ 250VAC
350mA @ 125VAC
6. OPERATING FORCE .8 ± .3 kg-cm
7. OPERATING TEMP: -30°C to 85°C
- ▲ 8. CIRCUIT SP: 3 POSITION 30° INDEX.
9. DIELECTRIC STRENGTH: 500VAC FOR 1 MIN.
- ▲ 10. HARDWARE SUPPLIED ON SWITCH: STOP RING, LOCKWASHER, HEXNUT
11. ▲ DENOTES CRITICAL PARAMETER.

REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®				OBJECT ID
A	ECO-100099	RELEASE	06/14/21	JM	TITLE KC13B7.002NLS				100116935
					SCALE	DATE	DR	DWG	REV
					3:2	6/7/2021	JM	G510622	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED