



PART NO.	MATERIAL	COLOR
PCG-1-48	NYLON 66/6 (RMS-21)	NATURAL
PCG-2-48	ABS (RMS-09)	GRAY
PCG-3-48	ABS (RMS-09)	GRAY
PCG-4-48	RIGID PVC (RMS-04)	GRAY
PCG-5-48	RIGID PVC (RMS-04)	GRAY

*PARTS AVAILABLE BY SPECIAL ORDER ONLY


*PCG-1-48




*PCG-2-48




PCG-3-48



PCG-4-48



*PCG-5-48



NOTES:

1. ALL GUIDES TO ACCEPT A NOMINAL 1/16 (1.6) THICK BOARD
2. PCG-3, -4, AND -5 AVAILABLE WITH ADHESIVE BACKING. TO ORDER ADD "A" TO PART NO. EXAMPLE: PCG-XA-48
3. TAPE: $\frac{1}{16}$ (1.6) THICK, ACRYLIC ADHESIVE TAPE (RMS-15)
4. COLOR BLACK AVAILABLE BY SPECIAL ORDER. TO ORDER ADD "BK" TO END OF THE PART NO.

TO ORDER ADD "BK" TO END OF THE PART NO.			TITLE: PRINTED CARD GUIDES					DWG IN IN (MM)	
			TOLERANCES UNLESS NOTED .XX=±.02 .XXX=±.015 FRAC=±1/32 ANG=±1°	FILE # PCG	DWN: JK	DT: 4.18.00	FINAL		
I	SEE ECN # 1352 FOR CHANGES	SK 08.09.07		MAT'L: SEE TABLE	CHKD:	ENG:	PART #	PRINT TYPE	
H	SEE ECN # 1153	S.J. 4.13.06		RE: RICHCO INC.	RICHCO INC. ENG@RICHCO-INC.COM (773) 539-4060		SEE TABLE	CA	
-	SEE ENGINEERING FOR REV. A THRU G	-							
REV	DESCRIPTION	ENGR DATE							