








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER ECN-22-133133	11DEC2021	AK	SZ




DIM A		POSITION 2	POSITION 1	PART NUMBER
SOLDER TAIL LENGTH		INDICATOR COLOR FOR EACH HOUSING		
OBSOLETE	.100	YELLOW	GREEN	2-5406552-4
	.162	YELLOW	GREEN	2-5406552-1
OBSOLETE	.132	GREEN/YELLOW	GREEN/YELLOW	2-5406552-0
	.146	RED/GREEN	RED/GREEN	1-5406552-9
	.100	RED/YELLOW	RED/GREEN	1-5406552-8
OBSOLETE	.100	GREEN	-	1-5406552-7
	.126	RED/GREEN	RED/GREEN	1-5406552-6
	.100	SEE VIEW A (SHEET 2)	SEE VIEW A (SHEET 2)	1-5406552-5
	.100	RED	GREEN	1-5406552-4
	.100	GREEN/RED	GREEN/RED	1-5406552-3
	.120	YELLOW	GREEN	1-5406552-1
	.100	GREEN/ORANGE	YELLOW	5406552-9
	.100	GREEN/YELLOW	GREEN/YELLOW	5406552-8
	.100	GREEN/ORANGE	GREEN/ORANGE	5406552-7
OBSOLETE	.100	YELLOW	YELLOW	5406552-6
	.100	GREEN	GREEN	5406552-5
OBSOLETE	.100	GREEN	YELLOW	5406552-4
	.100	YELLOW	-	5406552-3
	.100	-	GREEN	5406552-2
	.100	YELLOW	GREEN	5406552-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG T. SPRINKLE/L.A.MAYER DWG J. WESTMAN 10MAY2005 10MAY2005		 TE Connectivity Ltd.	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.25[.01] 3 PLC ± 0.13[.005] 4 PLC ± — 4 ANGLES		NAME S.FLICKINGER 10MAY2005 INVERTED MODULAR JACK ASSEMBLY, 1X4, SHIELDED, PANEL GROUND, WITH LED	
		PRODUCT SPEC 108-1163-4 APPLICATION SPEC 114-2154		SIZE A1	
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1		CAGE CODE 00779	
		WEIGHT —		DRAWING NO C-5406552	
		CUSTOMER DRAWING		SCALE 4:1	
				SHEET 1 OF 2	
				REV. —	



SUGGESTED PRINTED CIRCUIT BOARD LAYOUT
(COMPONENT SIDE)



VIEW A
(1-5406552-5 ONLY)

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN T. SPRINKLE/L.A. MAYER CHK J. WESTMAN APVD S. FLICKINGER	10MAY2005 10MAY2005 10MAY2005	 TE Connectivity Ltd.			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		INVERTED MODULAR JACK ASSEMBLY, 1X4, SHIELDED, PANEL GROUND, WITH LED			