

## M23 P Hood cable to cable 11-17 mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 600 0703
Specification	M23 P Hood cable to cable 11-17 mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09156000703">https://b2b.harting.com/09156000703</a>

### Identification

Category	Hoods/Housings
Series	Circular connectors M23
Identification	Power
Type of hood/housing	Cable to cable housing
Description of hood/housing	EMC version

### Version

Size	M23
Version	Top entry
Locking type	Screw locking ComLock rapid locking

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69 / IPX9K acc. to ISO 20653 locked condition
Clamping range	11 ... 17 mm

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Colour (seal)	Black
RoHS	compliant with exemption



Pushing Performance

## Material properties

RoHS exemptions 6(c): Copper alloy containing up to 4 % lead by weight

ELV status compliant with exemption

China RoHS 50

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances Yes

REACH SVHC substances Lead

California Proposition 65 substances Yes

California Proposition 65 substances Lead

## Specifications and approvals

UL / CSA UL 1977 ECBT2.E235076

## Commercial data

Packaging size 5

Net weight 67.1 g

Country of origin Germany

European customs tariff number 85366990

eCl@ss 27440224 Shell for circular connectors