



HEX/Allen screw



view of the hood without lid



Cable diameter without rubber bushing:
 $\varnothing F$ min: 3 mm
 $\varnothing F$ max: 12 mm

Cable diameter with rubber bushing:
 $\varnothing F$ max: 9,7 mm

Cable diameter without reduction plate:
 $\varnothing F$ max: 15 mm

		All Dimensions in mm Original Size DIN A4		Scale 1:1		Free size tol.		Ref.					
								Sub.					
		All rights reserved		Created by DOUGE		Inspected by BAGDIKIAN		Standardisation HOFFMANN		Date 2014-02-06		State Final Release	
		Department EC PD - FR											
		HARTING Electronics GmbH D-32339 Espelkamp		Title D-Sub 50-poles metal hood side entry								Doc-Key / ECM-Nr. 100566453/UGD/001/A 500000070497	
				Type TB		Number 09670500338						Rev. A	