

Between Series Adaptor 31_N-SMA-50-51/1--_N

Description

Adaptor jack/jack
N-precision jack (female) / SMA-precision jack (female)

For Test & Measurement applications
Precision adaptor

Interface standards
Series N-precision - IEC 60169-16_MIL-STD-348A/402_CECC 22210
Series SMA-precision - IEC 60169-15_MIL-STD-348A/405_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
VSWR	DC - 18 GHz ≤ 1.025 + 0.007 f (GHz)
Electrical length	32.97 mm

Mechanical Data

Number of matings	500
Weight	0.0331 kg

Environmental Data

Operating temperature	-55 °C to 70 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - N-precision jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	

Interface - SMA-precision jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	
Insulator		

Related Documents

Catalogue drawing	DCA-00014584
-------------------	--------------

Ordering Information

Single package	31_N-SMA-50-51/1--_NE
----------------	-----------------------

Remarks

Operating specification acc. IEEE Std 287: temperature 13 °C to 33 °C