







SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
B254W11-0B2P51-H85C32	2*1	0.00	2.54
B254W11-0B4P51-H85C32	2*2	2.54	5.08
B254W11-0B6P51-H85C32	2*3	5.08	7.62
B254W11-0B8P51-H85C32	2*4	7.62	10.16
B254W11-0B10P51-H85C32	2*5	10.16	12.70
B254W11-0B12P51-H85C32	2*6	12.70	15.24
B254W11-0B14P51-H85C32	2*7	15.24	17.78
B254W11-0B16P51-H85C32	2*8	17.78	20.32
B254W11-0B18P51-H85C32	2*9	20.32	22.86
.....			
B254W11-0B80P51-H85C32	2*40	(40-1)X2.54	(40)X2.54

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO. B254W11-0BXP51-H85C32	TITLE: 2.54FH H8.5 2xPin 90 度 Y型 PC3.2 PB12.7 6T		
.XX ±0.20	X.* ±1°				
.XXX ±0.10	X.XX* ±0.5°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1