

6

5





4

3


2

1

DIST	LOC	P	LTR	REVISION/RECORD	DATE	DWN	APVD
	EC		A	NEW RELEASE	JAN/22,07	SL	BW



SECTION A-A




SECTION B-B

NOTES:

1. ENAMEL WIRE APPLICATION RANGE:
Ø1.0~1.65mm.
2. INSULATION APPLICATION DATE:
Ø2.7mm MAX.
3. CONTINUOUS STRIP ON REEL.
4. CURRENT RATING COMPLY WITH UL486A RATING.

TOLERANCES UNLESS
OTHER SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.2
2 PLC ± 0.15
3 PLC ±
4 PLC ±
ANGLE ±

DIMENSIONS IN
mm

DR

STANLEY LU

DATE

NOV.1.2006

CHK

BORIS WONG

DATE

JAN.8.2007

APVD

BORIS WONG

DATE

JAN.8.2007

PRODUCT SPEC

108-58505

APPLICATION SPEC

114-58505

RESTRICTED TO

SCALE

1:1

SIZE

A4

DWG

NO.

C-1930001

BARE

1930001-1

FINISH

PART NUMBER

MATERIAL

COPPER ALLOY

FINISH

SEE TABLE

tyco
Electronics

Tyco Electronics
Hong Kong Limited

Room 1301, Ocean Centre No.
5 Canton Rd, Tsimshatsui Kowloon
Hong Kong

NAME

AMPLIVAR, (M3.5) RING TONGUE

SHEET
1 OF 1

REV
A

6

5

4

3

2

1