

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

COPYRIGHT

ALL RIGHTS RESERVED.

LOC DIST

REVISIONS

P LTR

DESCRIPTION

DATE

DWN


APVD

C1 REVISED PER ECO-11-005294


05APR11

RK

HMR



VIEW A




SECT B-B

注記


① 製品規格 108-5037

NOTE

① PRODUCT SPEC. 108-5037



VIEW A



SECT C-C

170120-4	リン青銅 0.32t	錫めっき済	170121-4
170120-1	黄銅 0.32t	錫めっき済	170121-1
型番	材料	仕上	LP型番

DIMENSIONS: 単位: 概 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED	
		一般公差	
		10% : ±0.2	
		30% : ±0.25	
		100% : ±0.3	
MATERIAL 材料		FINISH 仕上	
SEE TABLE 表参照		SEE TABLE 表参照	
DWN Y. TANAKA 8/FEB/'74		CHK T. IMAIZUMI 8/FEB/'74	
APVD Y. SATO 12/FEB/'74		PRODUCT SPEC	
APPLICATION SPEC		WEIGHT	
CUSTOMER DRAWING			

WIRE RANGE
包合電線断面積
0.50-2.27mm²/AWG#20-#14INSULATION DIA
被覆外径
MAX 3.3mm
最大 3.3mm

TE

TE Connectivity

MATE-N-LOK SOCKET
メイテンロック ソケット

SIZE A3 CAGE CODE 00779

DRAWING NO
番号
C- 170120

SCALE 4-1 SHEET 1 OF 1 REV C1

参考面