

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

LTR

DESCRIPTION

DATE _____

DWN

	APVD
--	------

A

REVISFD PFR FCO-10-013614

13OCT10

	HMP
--	-----

R	CR
---	----

NOTES:

MATERIAL:

HOUSING: THERMOPLASTIC, UL94V-0, BLACK.

TERMINALS: BRIGHT TIN OVER COPPER ALLOY.

SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE,
EXCEPT WHERE NOTED OTHERWISE.

ELECTRICAL:

RATED CURRENT UL/CSA:

CLASS C: 20A, 300V.

CLASS D: 5A, 600V.




WIRE RANGE: 12-22 AWG.

MECHANICAL:

RECOMMENDED TORQUE: 7 IN-LB.


OPERATING TEMP.: 105°C MAX.

 WHITE INK MARKING.



MOUNTING PANEL LAYOUT

3.375	3.689	8	JC6-Q308-08-131	7-1437665-0
DIM. L	DIM. A	NO. OF POS.	CATALOG NUMBER	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 3/7/05 CHK S YODER 3/7/05 APVD S YODER 3/7/05		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME JC6-Q308-08-131 ASSEMBLY	
		0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .010 4 PLC ± - ANGLES ± -			
MATERIAL -		FINISH -		SIZE A3	CAGE CODE 00779
		WEIGHT -		DRAWING NO C-7-1437665-0	
CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 1
				REV A	RESTRICTED TO -